

# Rittal – The System.

Faster – better – everywhere.



## AX 2820.061

Base/plinth corner piece with base/  
plinth trim panels, front and rear,  
100 mm

State: 3/9/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2820.061 - Base/plinth corner piece with base/plinth trim panels, front and rear, 100 mm for AX

Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | AX 2820.061   |
| Product description   | Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.  |
| Material              | Base/plinth corner piece: Sheet steel<br>Base/plinth trim panel front/rear: Sheet steel<br>Corner cover: Plastic  |
| Colour                | RAL 9005  |
| Supply includes       | 4 base/plinth corner pieces, 100 mm high<br>4 corner covers<br>2 base/plinth trim panels, front/rear, 100 mm high<br>Assembly parts   |
| Note                  | Base/plinth elements are required at the side to finish off a base/plinth unit<br>Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system |
| Dimensions            | Height: 100 mm  |
| To fit                | Enclosure type: AX<br>Width: = 600 mm   |
| Type rating to UL 50E | Type 1<br>Type 3R<br>Type 4<br>Type 12  |
| Packs of              | 2 pc(s).  |
| Net weight            | 4   |

# Features

|                       |               |
|-----------------------|---------------|
| Customs tariff number | 94039910      |
| EAN                   | 4028177942608 |
| ETIM 9                | EC000721      |
| ETIM 8                | EC000721      |
| ECLASS 8.0            | 27182003      |

# Approvals

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|