

# Rittal – The System.

Faster – better – everywhere.



## SO 2890.000 Levelling feet

State: 4/4/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SO 2890.000 - Levelling feet for base/plinth TS, stainless steel and base/plinth, complete, stainless steel

For direct mounting underneath the TS base/plinth and the base/plinth, complete. For unhindered access e.g. when cleaning the floor, and to compensate for floor irregularities.

## Features

|   |  |
|---|--|
| Model No.                                 | SO 2890.000  |
| Product description                       | For direct mounting underneath the base/plinth TS and the base/plinth, complete. For unhindered access e.g. when cleaning the floor, and to compensate for floor irregularities. |
| Benefits                                  | Unhindered access, e.g. for floor cleaning<br>To compensate for height differences with floor irregularities   |
| Material                                  | Stainless steel 1.4301 (AISI 304)  |
| Installation options                      | For direct mounting underneath the base/plinth TS and the base/plinth, complete  |
| Max. load capacity (static) per component | 400 kg   |
| Dimensions                                | Thread: M16  |
| Levelling range                           | 45 - 120 mm  |
| Packs of                                  | 4 pc(s).   |
| Net weight                                | 2.4 kg   |
| Gross weight                              | 2.74 kg  |
| Customs tariff number                     | 73181900   |
| ETIM 9                                    | EC000721   |
| ETIM 8                                    | EC000721   |
| ECLASS 8.0                                | 27182003   |
| Product description                       | SO Levelling foot, for TS, base/plinth complete, thread M16, stainless steel 1.4301  |