

Rittal – The System.

Faster – better – everywhere.



SO 2890.000 Levelling feet

State: 26/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SO 2890.000 - Levelling feet for base/plinth TS, stainless steel and base/plinth, complete, stainless steel

For direct mounting underneath the TS base/plinth and the base/plinth, complete. For unhindered access e.g. when cleaning the floor, and to compensate for floor irregularities.

Features

Model No.	SO 2890.000
Product description	For direct mounting underneath the base/plinth TS and the base/plinth, complete. For unhindered access e.g. when cleaning the floor, and to compensate for floor irregularities.
Benefits	Unhindered access, e.g. for floor cleaning To compensate for height differences with floor irregularities
Material	Stainless steel 1.4301 (AISI 304)
Installation options	For direct mounting underneath the base/plinth TS and the base/plinth, complete
Max. load capacity (static) per component	400 kg
Dimensions	Thread: M16
Levelling range	45 - 120 mm
Packs of	4 pc(s).
Net weight	2.4 kg
Gross weight	2.74 kg
Customs tariff number	73181900
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	SO Levelling foot, for TS, base/plinth complete, thread M16, stainless steel 1.4301