

Rittal – The System.

Faster – better – everywhere.



SV 3073.000 Busbar support

State: 22/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3073.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



Features

| | |
|-----------------------|---|
| Model No. | SV 3073.000 |
| Material | Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Number of poles | 3-pole 100 mm |
| To fit busbars | 30 x 10 40 x 10 50 x 10 60 x 10 |
| Rated current max. | 1,250 A |
| Dimensions | Width: 22 mm Height: 320 mm Depth: 70 mm |
| Packs of | 4 pc(s). |
| Net weight | 1.612 kg |
| Gross weight | 1.83 kg |
| Customs tariff number | 85469010 |
| ETIM 9 | EC001166 |
| ETIM 8 | EC001166 |

Features

ECLASS 8.0

27400607

Product description

SV Busbar support, 3-pole, 100 mm bar centre distance, for busbar
WH: 30-60x10 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

SV busbar support

for accommodating busbars. 3-pole busbar support
with 100 mm bar centre distance.

Rated operating voltage: 1000 V~, 50/60 Hz
to VDE 0660

Rated current: up to 1250 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 100 mm

Bar accommodation without inserts: 60 x 10 mm

Tightening torques

Assembly screws: 8 - 10 Nm

Lid attachment: 1 - 3 Nm

Approvals:

DNV, GL, VDE, ÖVE, SEV, KEMA