## Rittal – The System.

Faster – better – everywhere.





# SK 3130.115 TopTherm air-air heat exchanger

State: 15/12/2025 (Source: rittal.com/in-en)



# SK 3130.115 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

#### **Features**

Model No.	SK 3130.115
Design	wall-mounted
Product description	Air/air heat exchangers are particularly well-suited to aggressive ambient conditions, because the internal and external air circuits are completely separate from one another.
Colour	RAL 7035
Supply includes	Complete unit ready for connection Plug-in terminal strip Floating fault signal contact in case of overtemperature Drilling template Assembly parts
Specific thermal output	90 W/K
Air throughput (unimpeded air flow)	External circuit with 50 Hz: 850 m³/h External circuit with 60 Hz: 945 m³/h Internal circuit at 50 Hz: 850 m³/h Internal circuit at 60 Hz: 945 m³/h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Dimensions	Width: 400 mm Height: 1,580 mm Depth: 215 mm
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Temperature control	Electronic control with digital display (factory setting +35 °C)
Operating temperature range	-5 °C55 °C
IP protection category to IEC 60 529	Internal circuit IP 54 External circuit IP 34

© Rittal 2025

## Features

Packs of	1 pc(s).
Net weight	24.1
Gross weight	24.95
Customs tariff number	84158300
EAN	4028177425125
ETIM 9	EC002514
ETIM 8	EC002514
ECLASS 8.0	27180711

# **Approvals**

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3