

Rittal – The System.

Faster – better – everywhere.



SK 3164.230 Roof-mounted fans

State: 19/6/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3164.230 - Roof-mounted fans for VX, VX IT

Roof-mounted fan for the office sector with exceptionally low noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m³/h).



Features

Model No.	SK 3164.230
Benefits	Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs Fully wired ready for connection
Material	Sheet steel, spray-finished
Colour	RAL 7035
Supply includes	Roof-mounted fans Assembly parts
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 0.3 A At 60 Hz: 0.35 A
Dimensions	Width: 511 mm Height: 227 mm Depth: 511 mm
IP protection category to IEC 60529	Internal circuit IP 54
Note	Reduction in the specified air throughput to 800 m ³ /h at 40 Pa counterpressure using two vented base/plinth trim panels
Operating temperature range	20 °C...55 °C
Packs of	1 pc(s).

Features

Net weight	18.35 kg
Gross weight	19.36 kg
Customs tariff number	84145915
ECLASS 8.0	27180716
Product description	DK Roof-mounted fan, without roof plate, for TS and TS IT in the office sector, Required mounting cut-out: WxD: 410x410 mm, WHD: 511x227x511 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	-----------------------------------------------------------