Rittal – The System.

Faster – better – everywhere.





SK 3173.100 Chopped-fibre filter mat

State: 11/11/2025 (Source: rittal.com/in-en)



SK 3173.100 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Model No.	SK 3173.100	
Design	for filter fans	
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 μm.	
Material	Chemical fibres	
Note	No suitable for use in EMC filter fans.	
To fit Model No.	3243 3244 3245	
Dimensions	Width: 289 mm Height: 289 mm Depth: 17 mm	
Filter class	to DIN EN 779: G3 to DIN EN ISO 16890: ISO Coarse 50%	
Packs of	5 pc(s).	
Net weight	0.1	
Gross weight	0.12	
Customs tariff number	56039390	
EAN	4028177038134	
E-Number Sweden	E3404749	
ETIM 9	EC002513	
ETIM 8	EC002513	

© Rittal 2025

Features

ECLASS 8.0	27180706

Approvals

Approvals	UR + C-UR (recognized)
Certificates	EAC

© Rittal 2025 3