

Rittal – The System.

Faster – better – everywhere.



SK 3238.200

Outlet filter

State: 18/1/2026 (Source: [ittal.com/in-en](https://www.ittal.com/in-en))



FRIEDHELM LOH GROUP

SK 3238.200 - Outlet filter Standard

For ventilation by convection, an outlet filter can be fitted in both the upper and lower sections of the enclosure.



Features

| | |
|--------------------------|--|
| Model No. | SK 3238.200 |
| Product description | For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure. |
| Material | ABS |
| Colour | RAL 7035 |
| Supply includes | Outlet filter Chopped-fibre filter mat |
| Mounting cut-out | Cut-out width: 124 mm Cut-out height: 124 mm |
| To fit Model No. | SK 3238.1xx |
| Dimensions | Width: 148.5 mm Height: 148.5 mm Depth: 24 mm |
| Protection category NEMA | Type 1 with pleated filter Type 12 with chopped-fibre filter Type 3 Type 3R Type 4 Type 4X with chopped-fibre filter/pleated filter and hose-proof hood |

Features

| | |
|--------------------------------------|--|
| IP protection category to IEC 60 529 | IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood |
| Packs of | 1 pc(s). |
| Net weight | 0.17 |
| Gross weight | 0.18 |
| Customs tariff number | 39269097 |
| EAN | 4028177651739 |
| E-Number Sweden | E3404349 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |

Approvals

| | |
|--------------|---|
| Approvals | CSA UL + C-UL - FTTA UR + C-UR (recognized) |
| Certificates | EAC |
| Explanations | Declaration of conformity |
