

Rittal – The System.

Faster – better – everywhere.



SK 3239.824 Blue e+ filter fan

State: 17/7/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3239.824 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20 – 900 m³/h



Features

| | |
|---|---|
| Model No. | SK 3239.824 |
| Design | wall-mounted EMC |
| Product description | EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3. |
| Benefits | Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly |
| Material | Plastic |
| Colour | RAL 7035 |
| Supply includes | Complete unit ready to install, including EMC filter mat |
| Fan | Axial, DC motor |
| Air throughput, unimpeded airflow (with chopped-fibre filter) | With DC: 100 m ³ /h |

Features

| | |
|---|--|
| Air throughput with matching outlet filter including chopped-fibre filter | With DC: 75 m³/h |
| Rated operating voltage | 24 V (DC) |
| Power consumption Pel | With DC: 5.7 kW |
| Rated current max. | With DC: 0.27 A |
| Dimensions | Width: 204 mm Height: 204 mm Depth: 105 mm |
| Installation depth | 84 mm |
| Mounting cut-out | Cut-out width: 177 mm Cut-out height: 177 mm |
| IP protection category to IEC 60 529 | IP 54 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood |
| Protection category NEMA | Type 12 with chopped-fibre filter Type 3, 3R, 4, 4X with chopped-fibre filter and hose-proof hood |
| Pre-fuse | Miniature circuit-breaker/fuse: 2 A |
| Note | To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays |
| Operating temperature range | -15 °C...55 °C |
| Storage temperature range | -30 °C...70 °C |
| Noise level | With DC: 51 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 1.1 |
| Gross weight | 1.24 |
| Customs tariff number | 84145915 |
| EAN | 4028177985537 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27180716 |
|------------|----------|

Approvals

| | |
|--------------|---|
| Approvals | 30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized) |
| Explanations | Declaration of conformity |
