


# Rittal – The System.

Faster – better – everywhere.



## SK 3352.024

## Vario rack-mounted fans for 482.6 mm (19")

State: 3/7/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3352.024 - Vario rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m<sup>3</sup>/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. Guide frame ensures easy maintenance of the fan.

## Features

Model No.	SK 3352.024
Product description	Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.
Benefits	Guide frame ensures easy maintenance and replacement of the fans
Colour	RAL 7035
Supply includes	Fully wired unit ready for connection Terminal strip and assembly parts
Air throughput (unimpeded air flow)	480 m <sup>3</sup> /h
Note on Model No.	Extended delivery times.
Rated operating voltage	24 V (DC)
Rated current max.	With DC: 0.74 A
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Dimensions	Width: 482.6 mm Height: 44 mm Depth: 200 mm
Distance between axes of fans	105 mm
No. of fans	3
Noise level	With DC: 51 dB(A)
Operating temperature range	-10 °C...55 °C

# Features

Packs of	1 pc(s).
Net weight	1.64
Gross weight	1.84
Customs tariff number	84145915
EAN	4028177041639
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

# Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK