
Rittal – The System.

Faster - better - everywhere.





AS 4050.730 Wire end ferrules

State: 13/12/2025 (Source: rittal.com/in-en)



AS 4050.730 - Wire end ferrules loose

With plastic collar.

Features

| Model No. | AS 4050.730 | |
|--------------------------|--|--|
| Product description | With plastic collar. | |
| Technical specifications | Heat-resistant to 105 °C | |
| Material | E-Cu, galvanic tin-plated Plastic collar: Polypropylene | |
| Colour | White | |
| Length | 8 mm | |
| AWG | 20 | |
| Internal diameter | 2.6 mm | |
| For cross-section | 0.5 mm² | |
| DIN colour code | Yes | |
| Note | UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant. | |
| Standards | AEH DIN 46228 | |
| To fit Model No. | 4051.205 4051.210 4050.452 | |
| Delivery form | Loose | |
| Packs of | 500 pc(s). | |
| Net weight | 0.5 | |
| Gross weight | 0.5 | |
| Customs tariff number | 85369010 | |
| EAN | 4028177804982 | |
| | | |

© Rittal 2025

Features

| ETIM 9 | EC000005 | |
|------------|----------|--|
| ETIM 8 | EC000005 | |
| ECLASS 8.0 | 36659290 | |

Approvals

| Approvals | UL + C-UL (listed) |
|-----------|--------------------|
| | UR |

© Rittal 2025 3