## Rittal – The System.

Faster - better - everywhere.





# AS 4050.784 Wire end ferrules

State: 7/12/2025 (Source: rittal.com/in-en)



## AS 4050.784 - Wire end ferrules loose

With plastic collar.

#### **Features**

| Model No.                | AS 4050.784  |
|--------------------------|--|
| Product description      | With plastic collar.   |
| Technical specifications | Heat-resistant to 105 °C   |
| Material                 | E-Cu, galvanic tin-plated Plastic collar: Polypropylene  |
| Colour                   | Grey   |
| Length                   | 18 mm  |
| AWG                      | 12   |
| Internal diameter        | 4.8 mm   |
| Rittal colour code       | Yes  |
| DIN colour code          | Yes  |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant. |
| Standards                | AEH DIN 46228  |
| Delivery form            | Loose  |
| Packs of                 | 100 pc(s).   |
| Net weight               | 0.1  |
| Gross weight             | 0.041  |
| Customs tariff number    | 85369010   |
| EAN                      | 4028177000018  |
| ETIM 9                   | EC000005   |
| ETIM 8                   | EC000005   |
|                          |  |

© Rittal 2025 2

### Features

ECLASS 8.0 36659290

# **Approvals**

Approvals UL + C-UL (listed) UR

© Rittal 2025

3