

**Rittal – The System.**

Faster – better – everywhere.



# AS 4055.263

## Hole punch, round

State: 11/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.263 - Hole punch, round for sheet steel

For punching round cut-outs

## Features

|  |   |
|--|---|
| Model No.  | AS 4055.263   |
| Design   | With 3 cutting points   |
| Product description                                | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.   |
| Supply includes                                    | Female dies<br>Male dies<br>Tension screw without ball bearing  |
| Machinable material                                | Sheet steel   |
| Maximum machinable material thickness, sheet steel | 3 mm  |
| Ø punch  | 63.5 mm   |
| For threads  | M63   |
| Note   | When operating with wrenches, tension screws with ball bearings should be used.<br>Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number           | 4055.663  |
| Tension screw (Ø x L)                              | 19 x 75 mm  |
| Hydraulic tension screw Ø                          | 19 mm   |
| Packs of   | 1 pc(s).  |
| Net weight   | 1.175 kg  |
| Gross weight                                       | 1.249 kg  |
| Customs tariff number                              | 82073010  |
| ETIM 9   | EC000156  |
| ETIM 8   | EC000156  |

# Features

---

ECLASS 8.0

21049047

---

Product description

Sheet metal punch round Ø 63,5 mm