### Rittal - The System.

Faster – better – everywhere.





## AS 4055.522 Splitter hole punch, round

State: 13/12/2025 (Source: rittal.com/in-en)



# AS 4055.522 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

#### **Features**

Model No.	AS 4055.522
Design	With triple splitting
Product description	
Supply includes	Female dies Male dies
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm
Ø punch	22.5 mm
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9.5 mm 19 mm
Packs of	1 pc(s).
Net weight	0.088
Gross weight	0.108
Customs tariff number	82073010
EAN	4028177808676
ETIM 9	EC000156

© Rittal 2025

### **Features**

ETIM 8	EC000156	
ECLASS 8.0	21049047	

© Rittal 2025 3