

Rittal – The System.

Faster – better – everywhere.



AS 4055.582

Splitter hole punch set, PG 9 to PG 21

State: 26/8/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.582 - Splitter hole punch set, PG 9 to PG 21 for sheet steel, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.582
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	6 female dies 6 male dies 2 tension screws with ball bearing Ø 9.5 x 50 mm HSS pilot drill Ø 10 mm 1 tube of lubricant paste Plastic case
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm
Ø punch	15.2 mm 18.6 mm 20.4 mm 22.5 mm 28.3 mm 30.5 mm
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.661
Packs of	1 pc(s).
Net weight	1.08
Gross weight	1.09

Features

Customs tariff number	82073010
EAN	4028177808850
ECLASS 8.0	21044719