

# Rittal – The System.

Faster – better – everywhere.



## SZ 4138.400 Standard light

State: 21/5/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4138.400 - Standard light

Supply voltage: 120 V AC 60 Hz, 230 V AC 50 Hz

## Features

|  |   |
|--|---|
| Model No.  | SZ 4138.400   |
| Design   | without door operated switch  |
| Supply includes                                    | Standard light<br>Light<br>Assembly parts   |
| Power consumption                                  | 30 W  |
| Ballast  | Magnetic ballast  |
| Connection options                                 | Door-operated switch<br>Power supply via connectors<br>Through-wiring (creating rows of lights)   |
| Light  | Fluorescent lamp, base G13  |
| Protection class                                   | I (PE conductor)  |
| Switch (type)                                      | Integral on/off/door-operated switch  |
| Light – installation type                          | Screw-fastening   |
| Rated impulse withstand voltage,<br>phase to earth | 1500 V AC   |
| Rated impulse withstand voltage,<br>phase to phase | 1000 V AC   |
| Rated insulation voltage                           | 500 V DC/1s   |
| Installation options                               | TS horizontal section of the roof frame: direct<br>TS, SE vertical section: with TS adaptor bracket<br>SE sections at the front and rear of the roof frame: with TS adaptor bracket<br>SE extrusions at the side of the roof frame: direct<br>AE, CM, TP: with universal bracket<br>AE: with rail for interior installation |

## Features

|                             |   |
|-----------------------------|---|
| Dimensions                  | Width: 987 mm<br>Height: 117 mm<br>Depth: 50 mm |
| Operating temperature range | -15 °C...45 °C                                  |
| Sockets                     | USA/CDN (type B, NEMA 5-15)                     |
| Storage temperature range   | -20 °C...70 °C                                  |
| Rated operating voltage     | 120 V, 1~, 60 Hz                                |
| Socket version              | USA/CDN (type B, NEMA 5-15)                     |
| Packs of                    | 1 pc(s).  |
| Net weight                  | 2.83  |
| Gross weight                | 2.84  |
| Customs tariff number       | 94054990  |
| EAN                         | 4028177581432                                   |
| ECLASS 8.0                  | 27189241  |

## Approvals

|           |  |
|-----------|--|
| Approvals | UL + C-UL (listed)<br>UR + C-UR (recognized) |
|-----------|--|