



PS 4826.500 - PS 4000 baying system

Baying Systems PS 4000 with mounting plate. Protection category IP 55.

Features

Model No.	PS 4826.500
Product description	Baying Systems PS 4000 with mounting plate. Protection category IP 55
Material	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Mounting plate: Sheet steel with zinc coating, 3.0 mm Gland plates: Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Door(s) Roof plate Rear panel, detachable 4 eyebolts, fitted Lock: 3 mm double-bit Base tray with gland plate, multi-piece, solid Mounting plate
Note	Net weight
Number of doors	1
Dimensions	Width: 800 mm Height: 2,200 mm Depth: 600 mm
Packs of	1 pc(s).

Approvals

Approvals

CSA

UL

Certificates

Protection category