

Rittal – The System.

Faster – better – everywhere.



PC 5366.200

PC enclosure system

State: 23/7/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 5366.200 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.

Features

Model No.	PC 5366.200
Design	with glazed door at the top, desk section and component shelf
Product description	Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.
Material	Enclosure, door, rear door, mounting compartment, supports: Sheet steel Handles, decorative trim panels: Plastic Door trim panels: Aluminium Viewing window: Single-pane safety glass
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting compartment, support: powder-coated
Colour	Enclosure, door, decorative trim panels, supports: RAL 7035 Handle: Similar to RAL 9006 Monitor panel, door centre part: RAL 7015
Supply includes	Enclosure, door, rear door Glazed door, top Desk section Component shelf
Dimensions	Width: 600 mm Height: 1,600 mm Depth: 636 mm
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 12

Features

Max. keyboard dimensions (WxHxD)	540 x 40 x 175 mm
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	93.5
Gross weight	95.5
EAN	4028177693234
ECLASS 8.0	27180501

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Enclosure system with monitor door and desk section

Enclosure for stand-alone siting, consisting of solid body, glazed door at the top, desk section, component shelf, bottom door, rear door and welded base assembly. Enclosure body with mounting angles at the front and rear.

System slots on a 25 mm pitch pattern, all round, for individual interior installation and two pairs of mounting angles for space-saving system configuration.

Glazed door, top:

With support frame latched from the inside, r/h hinge

- Vertical decorative trim panels
- Pane with screen-printed mask

Component shelf for monitor:

- Slotted, permanently installed

Desk section:

- Enclosure with removable cover top and bottom
- Trim strip, top and handle strip

Bottom door:

- Vertical bars with locking rod and double-bit insert
- Hinged on right-hand side
- Door or installation plate folded

Rear door:

- With locking rod and double-bit insert, hinged on right-hand side
- Gland plates, three-part

Material:

Enclosure, door, desk section, gland plates: Sheet steel

- Handles, decorative trim panels: Plastic
- Door trim panels: Aluminium

Surface finish:

- Zinc-plated gland plates

Colour:

- Enclosure, rear door: RAL 7035

Top glazed door:

- Vertical decorative trim panels: RAL 7035
- Pane with screen-printed mask: RAL 7015

Component shelf for monitor: RAL 7015

Desk section:

- Enclosure with removable cover top and bottom RAL 7035

- Trim strip, top and handle strip: RAL 7035/7015/9006

Bottom door:

- Vertical bars: RAL 7035

- Folded installation plate: RAL 7015

External dimensions WHD: 600 x 1600 x 600 mm

Model No.: 5366200

Manufacturer: Rittal GmbH & Co.KG