



Rittal – The System.

Faster – better – everywhere.



DK 5501.285

Mounting frame, 482.6 mm (19")

State: 5/5/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.285 - Mounting frame, 482.6 mm (19") for TS, TS IT

For the installation of the front and rear 482.6 mm (19") levels, the welded 482.6 mm (19") mounting frame may be attached with complete depth variability.



Features

| | |
|---------------------|---|
| Model No. | DK 5501.285 |
| Product description | Firmly linked 482.6mm (19") mounting frame for integration of a 482.6 mm (19") mounting level within a TS frame structure. Profiles analogous to TS IT for complete system compatibility, incl. tool-free assembly. Depth-variable mounting between the roof and base frames. Individual height units bi-directionally numbered. Mounting frame at the front, prepared for the integration of cable management and Dynamic Rack Control (RFID), mounting frame at the rear for space-saving integration of the PDU busbar, in the Zero-U space on both sides. |
| Material | Sheet steel |
| Surface finish | Primed |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Units | 47 U |
| Mounting position | rear |
| Load capacity | Up to 15,000 N static load, with even load distribution on two 482.6 mm (19") mounting frames, fully configured. |

Features

| | |
|-----------------------|---|
| Note | The outer mounting level of the enclosure frame is left free for other installed equipment. All-round compartmentalisation with air baffle plates is supported. |
| To fit | Enclosure type: TS TS IT Width: 600 mm Height: 2,200 mm |
| Packs of | 1 pc(s). |
| Net weight | 12 |
| Gross weight | 15 |
| Customs tariff number | 73269098 |
| EAN | 4028177716506 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |