


# Rittal – The System.

Faster – better – everywhere.



## DK 5501.292

## Mounting frame, 482.6 mm (19")

State: 15/4/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.292 - Mounting frame, 482.6 mm (19") for TS, TS IT

For the installation of the front and rear 482.6 mm (19") levels, the welded 482.6 mm (19") mounting frame may be attached with complete depth variability.



## Features

Model No.	DK 5501.292
Product description	Firmly linked 482.6mm (19") mounting frame for integration of a 482.6 mm (19") mounting level within a TS frame structure. Profiles analogous to TS IT for complete system compatibility, incl. tool-free assembly. Depth-variable mounting between the roof and base frames. Individual height units bi-directionally numbered. Mounting frame at the front, prepared for the integration of cable management and Dynamic Rack Control (RFID), mounting frame at the rear for space-saving integration of the PDU busbar, in the Zero-U space on both sides.
Material	Sheet steel
Surface finish	Primed
Colour	RAL 9005
Supply includes	Assembly parts
Units	47 U
Mounting position	front
Load capacity	Up to 15,000 N static load, with even load distribution on two 482.6 mm (19") mounting frames, fully configured.

# Features

Note	The outer mounting level of the enclosure frame is left free for other installed equipment. All-round compartmentalisation with air baffle plates is supported.
To fit	Enclosure type: TS TS IT Width: 800 mm Height: 2,200 mm
Packs of	1 pc(s).
Net weight	14.6 kg
Gross weight	16.6 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Mounting frame, 482.6 mm (19"), For WxH: 800x2200 mm, At the front, RAL 9005