Rittal - The System.

Faster – better – everywhere.





SM 6450.010 TFT monitor

State: 17/11/2025 (Source: rittal.com/in-en)



SM 6450.010 - TFT monitor

Installation variant for surfaces and command panels.

Features

Model No.	SM 6450.010
Design	without touchscreen
Product description	Installation variant for surfaces and command panels.
Benefits	High-quality industrial design Reduced installation work thanks to integral front frame No additional ventilation required Very small installation depth (45 mm)
Material	Front frame: Aluminium
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Seal Hex nuts (for installation in surfaces) VGA cable Threaded bolt M5, for rear mounting Touch variants additionally with integral connection cable and CD-ROM driver With anti-reflection coated safety glass screen.
Dimensions	Width: 430 mm Height: 343 mm
Interfaces	VGA (D-Sub HD 15-pole) DVI-D
Operating temperature range	0 °C50 °C
Storage temperature range	-40 °C85 °C
Display brightness	400 cd/m ²
Contrast ratio	700 : 1

© Rittal 2025

Features

50,000 h
Operating buttons at the rear
80 °
1024 x 768 pixels
With DC: 15 W
31.4 - 80 kHz
60 - 75 Hz
16.7
VGA
SVGA
XGA
1 pc(s).
6.4
6.52
85286200
4028177389991
EC001428
19200201

Approvals

·	Explanations	Declaration of conformity
---	--------------	---------------------------

© Rittal 2025 3