

Rittal – The System.

Faster – better – everywhere.



TP 6700.600 Pedestals

State: 23/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 6700.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

Model No.	TP 6700.600
Material	Enclosure: Sheet steel 1.5 mm Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Sheet steel
Surface finish	Enclosure, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure open at top Door or double door with locking rod (with depth 400 mm at the front, with depth 500 mm at the front and rear) Mounting plate Gland plates
Dimensions mounting plate (W x H)	499 mm x 625 mm
Number of doors	1
Dimensions	Width: 600 mm Height: 675 mm Depth: 400 mm
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Note	Positioning slide VX 5051.172 can be used as a mounting aid for base/plinth system VX in its new design
Packs of	1 pc(s).

Features

Net weight	34.5 kg
Gross weight	35 kg
Customs tariff number	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	TP TopConsole system, pedestal, WHD: 600x675x400 mm, Sheet steel

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK