

# Rittal – The System.

Faster – better – everywhere.



## DK 7072.230

## Nylon loop

State: 23/5/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7072.230 - Nylon loop

With the nylon loop, secured cables are easily released, allowing individual cables to be added or removed, ideal for sensitive data cables (fibre-optic/Cu).

## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7072.230   |
| Product description   | With the nylon loop, secured cables are easily released, allowing individual cables to be added or removed. Ideal for sensitive data cables (fibre-optic/Cu), as it avoids indentations on the cable sheathing. In addition, the nylon loop may be screw-fastened to the round system punchings or attached using a quick-release fastener. |
| Colour                | Black   |
| Supply includes       | Quick-release fastener  |
| Dimensions            | Width: 20 mm<br>Length: 200 mm  |
| Max. cable diameter   | 50 mm   |
| Packs of              | 10 pc(s).   |
| Net weight            | 0.03 kg   |
| Gross weight          | 0.041 kg  |
| Customs tariff number | 58061000  |
| ETIM 9                | EC002625  |
| ECLASS 8.0            | 27189234  |
| Product description   | DK Nylon loop, WxL: 20x200 mm, For Ø: 50 mm   |

# Tender text

Nylon loop for cable routing, max. cable diameter 50 mm

The nylon loop is attached to cable clamp rails, C rails, system rails or to the enclosure frame. The nylon loop may be screw-fastened as per the 25 mm DIN pitch pattern. The nylon loop can hold cable bunches up to 50 mm in diameter; single cables can easily be added or detached.

Nylon loop length: 200 mm

Max. cable diameter: 50 mm