

Rittal – The System.

Faster – better – everywhere.



DK 7502.446

QuickBox, 482.6 mm (19")

State: 8/12/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7502.446 - QuickBox, 482.6 mm (19")

Wall-mounted enclosure with removable cover for simple installation and horizontal 482.6 mm (19") level. Status monitoring via viewing window.

Features

Model No.	DK 7502.446
Design	with glazed door
Product description	Wall-mounted enclosure with removable cover for perfect handling during installation and maintenance.
Material	Wall mounting plate with mounting brackets: Sheet steel, 2.0 mm Enclosure cover: Sheet steel, 1.0 mm Door: Sheet steel door or glazed door with sheet steel frame and single-pane safety glass, 3 mm
Surface finish	Enclosure: Powder-coated
Colour	RAL 7035
Supply includes	Wall section: with pre-configured mounting brackets, brush strip for cable entry at the bottom/top, cable clamp rail, 482.6 mm (19") mounting angles, fully depth adjustable Enclosure cover: Base and cover tray with vent slots, brush strip for cable entry at the top/bottom, 2 side security locks, sheet steel door or glazed door with security lock 12321, version with Ergoform-S lock system, may optionally be retrofitted with semi-cylinder.
Units	15 U
Dimensions	Width: 600 mm Height: 762 mm Depth: 600 mm
Installation depth	547 mm
Depth of wall section	755 mm
Width wall section	595 mm
Basic material	Sheet steel

Features

Note on Model No.	With Ergoform-S lock system for semi-cylinder and security lock 3524 E, for combining with quick-release fastener QB 7502.220.
Packs of	1 pc(s).
Net weight	39.805
Gross weight	41.9
Customs tariff number	94032080
EAN	4028177597402
ECLASS 8.0	27180208

Tender text

15 U Wall-mounted enclosure

Wall section:

With pre-assembled mounting brackets
on the left and right hand side for
attachment of 482.6 mm (19") mounting angles
and for accommodation of cable routing accessories.

One set of 482.6 mm (19") mounting angles,
screw-fastened to mounting brackets,
infinitely depth-variable, optional second level, one
static T-head strip each at top and bottom in the
cable entry section.

Four holes for direct wall mounting or by optional
wall mounting brackets.

Enclosure cover with glazed door:

Enclosure cover with side vent slots in base and cover
tray for passive ventilation.

Openings in the top and bottom rear section for cable
entry, covered by brush strips, internal cover lock,
only accessible when the front door is open.

Glazed door with swing lever handle system Ergoform-S
with security lock 3524 E, exchangeable for
semi-cylinders to DIN 18 252.

Material: Sheet steel

Viewing panel: Toughened safety glass 3 mm

Surface finish: Enclosure powder-coated in RAL 7035

Sizes: W x H x D 600 x 762 x 600 mm / (15 U)