

Rittal – The System.

Faster – better – everywhere.



DK 7608.510

Socket strip in a plastic housing

State: 18/12/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7608.510 - Socket strip in a plastic housing

Socket strips 230 V, unrestricted use, including angular connectors, thanks to the long row arrangement of plug-type contacts.



Features

Model No.	DK 7608.510
Product description	8-way socket strip for earthing-pin plug (type F, CEE 7/4) The strip may be mounted vertically on the enclosure frame or in the rear 482.6 mm (19") section. In the 482.6 mm (19") section, more than 2 U of space is required. The sockets are arranged at an angle of 45° so that angular connectors are also easily used. The connection cable is contacted in a terminal slot in the strip. The terminal slot has a separate cover and external terminals for separate earthing.
Material	Plastic
Supply includes	Connection cable Assembly screws 2 serrated washers Captive nuts M6, conductive Nuts
Design	Without switch
Sockets	12 x CH (type J, SEV 1011)
Dimensions	Length: 793 mm
Length of connection cable	2 m
Connection cable (type)	H05VV-F3G1.5 with wire end ferrules

Features

Rated operating voltage	230 V AC, 50 Hz
Rated voltage	230 V AC, 50 Hz
Rated current (max.)	10 A
Installation options	Components with a 25 mm pitch pattern Enclosure frame
Packs of	1 pc(s).
Net weight	1.6
Gross weight	1.8
Customs tariff number	85366990
EAN	4028177162709
ETIM 9	EC000330
ECLASS 8.0	27142604

Tender text

230 V socket strip with 12 sockets (CH)

This socket strip has been designed for CH. There are 12 sockets available for use in the CH version. The enclosure is made from halogen-free plastic. It can easily be integrated in a network or server enclosure.

Technical specifications:

Rated voltage: 250 V

Rated current: 10 A

2 m connection cable, without connecting plug,
H05VV-F3G1.5