### Rittal - The System.

Faster – better – everywhere.





# DK 7709.535 Wall-mounted enclosures EL, 3-part

State: 28/11/2025 (Source: rittal.com/in-en)



## DK 7709.535 - Wall-mounted enclosures EL, 3-part preconfigured with mounting angles, depth-variable

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, earth rail, wall-mounting bracket

#### **Features**

Model No.	DK 7709.535
Design	Wall-mounted enclosures IT
	pre-configured with mounting angles, depth-variable
Product description	Wall-mounted enclosure with optimum accessibility due to hinged
	part.
Material	Wall and hinged part: Sheet steel, 1.5 mm
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General colour	RAL 7035
Colour	Wall and hinged part: RAL 7035
	Glazed door: RAL 7035/7015 (slate grey)
Supply includes	Wall section with solid gland plate at the top and brush strip at the
	bottom, two vertical mounting rails and C rail, horizontal, for cable clamping
	Hinged part with 25 mm pitch pattern of holes in the front and real
	frame, two 482.6 mm (19") mounting angles at the front, infinitely
	depth-variable, and side outlet filters on the left and right
	Earth rail with star earthing
	Designer glazed door
	1 double-kit key no. 5
	Wall mounting bracket, 10 mm, reinforced
	Mini-comfort handle for lock inserts
	Security lock 3524 E
Units	9 U

© Rittal 2025 2

#### Features

Dimensions	Width: 600 mm Height: 478 mm Depth: 673 mm
Installation depth	620 mm
Clearances	Clearance width: 502 mm Clearance height: 415 mm
Depth hinged part	516 mm
Depth of wall section	135 mm
IK Code	IK08
Load capacity of hinged part (static)	450 N
Basic material	Sheet steel
Protection category to IEC 60 529	IP 54 in conjunction with solid gland plate top and bottom
Packs of	1 pc(s).
Net weight	36.1
Gross weight	38
Customs tariff number	94032080
EAN	4028177551015
E-Number Sweden	E7239958
ETIM 9	EC000261
ECLASS 8.0	27142408

# Approvals

Approvals	UL + C-UL (listed)
, .pp. 6 va. 6	02 * 0 02 (110:00)

### Tender text

© Rittal 2025 3

Wall-mounted enclosure, based on Rittal EL, 3-part, pre-configured, depth 673

#### Enclosure:

Three-part wall-mounted distributor enclosure, consisting of:

Wall-mounted with 2 vertical mounting rails and one horizontally mounted C rail for cable clamping, exchangeable gland plates, solid top and cable entry brush insert at bottom, fitted potential equalisation rail, two infinitely adjustable 482.6 mm (19") mounting angles, mounted on C rails, with all-round 25 mm punched profile in front and rear frames, outlet filter for passive enclosure ventilation fitted at the top on the right side and at the bottom on the left side, prepared for fitting of an active fan expansion kit, glazed door design with mini comfort handle for lock inserts, with 3524E security lock that can be changed for mini comfort handle for semi-cylinder (option), enclosure fully earthed using stars, 4 x 10 mm wall-mounting brackets included.

Protection category: IP 54 to EN 60 529 in conjunction with a solid gland plate, top and bottom. Hinged part load capacity: 45 kg

Material:

Enclosure: Sheet steel 1.5 mm

Viewing window: 3 mm single-pane safety glass

Surface finish:

Electrophoretic dipcoat, spray finished, enclosure RAL 7035, glazed door RAL 7035/7015 Dimensions (W x H x D): 600 x 478 x 673 mm, 9 U

© Rittal 2025 4