

Rittal – The System.

Faster – better – everywhere.



DK 7824.120

Side panel, lockable

State: 1/2/2026 (Source: [ittal.com/in-en](https://www.ittal.com/in-en))



DK 7824.120 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.



Features

| | |
|-----------------------|--|
| Model No. | DK 7824.120 |
| Product description | Simply locate from above. Lock with security lock no. 3524 E. Earthing bolt with contact track. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7035 |
| Supply includes | 2 side panels each with 4 security locks no. 3524 E |
| To fit | Enclosure type: TS TS IT Height: 1,200 mm Depth: 1,000 mm |
| Basic material | Sheet steel |
| Packs of | 2 pc(s). |
| Net weight | 28.6 |
| Gross weight | 29.8 |
| Customs tariff number | 94039910 |
| EAN | 4028177330672 |
| E-Number Sweden | E7239565 |
| ETIM 9 | EC002524 |

Features

ECLASS 8.0

27182101

Tender text

Side panel, plug-type for TS
H x D = 1200 x 1000 mm, RAL 7035

Side panel fitted with a T-lock.
Material: Sheet steel, spray finished in RAL 7035
For 1200 mm x 1000 mm enclosures