

Rittal – The System.

Faster – better – everywhere.



DK 7824.280

Sheet steel glazed door, vertically divided

State: 14/6/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.280 - Sheet steel glazed door, vertically divided for TS 8

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

| | |
|-------------------------------------|---|
| Model No. | DK 7824.280 |
| Product description | With underlaid viewing panel, 4-point locking rod and comfort handle for profile half-cylinders with security lock 3524 E. The divided design allows room-optimised siting of the enclosures coupled with the best possible access, thanks to a reduced distance between the individual bayed enclosure suites. Max. door opening angle thanks to pre-integrated 180° hinges. |
| Material | Frame: Sheet steel Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | Height 2200 mm cannot be combined with swing frame 45 U. |
| IP protection category to IEC 60529 | IP 55 |
| To fit | Enclosure type: TS 8 Width: 800 mm Height: 2,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 34 |
| Gross weight | 35.4 |
| EAN | 4028177570924 |
| ECLASS 8.0 | 27182204 |

Tender text

Sheet steel glazed door, vertically divided for TS
With underlaid viewing panel, 4-point locking rod
and comfort handle for semi-cylinder with security
lock 3524 E. Max. door opening angle 180°.

Material:

Sheet steel, viewing window toughened safety
glass, 4 mm

Colour: RAL 7035

For enclosures (W x H): 800 x 2000 mm