

Rittal – The System.

Faster – better – everywhere.



DK 7826.886

Roof plate, vented

State: 2/5/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.886 - Roof plate, vented for DK-TS, 97 mm high

In exchange for the standard roof.

Features

Model No.	DK 7826.886
Product description	In exchange for the standard roof. Ventilation holes (Ø 5 mm) are incorporated all-round into the 97 mm high roof plate. In conjunction with the vented glazed and sheet steel door, the roof plate coordinates perfectly with the door design.
Material	Sheet steel
Colour	RAL 7035
To fit	Enclosure type: DK-TS Width: 800 mm Depth: 800 mm
Packs of	1 pc(s).
Net weight	10.947
Gross weight	11.523
Customs tariff number	72092690
EAN	4028177234734
ECLASS 8.0	27182405

Tender text

DK TS 8 vented cable entry roof plate

75 mm high roof plate with all-round perforated plate (3 mm diameter) for passive ventilation.

The roof plate has been designed so that it fits the ventilated glazed and sheet steel doors.

Cable entry sliding angular bracket at the rear.

An optional side or front cable entry can be fitted as the symmetrical frame design enables the roof plate to be turned.

Rubber section for fixing the cables and cable bunches to the sliding and fixed brackets.

Active ventilation can be provided by retrofitting a fan plate to the base.

Material: Sheet steel

Spray finish: RAL 7035

for enclosure dimensions: W: 800 mm D: 800 mm