Rittal - The System.

Faster – better – everywhere.



TS 8610.805 Glazed door

State: 14/12/2025 (Source: rittal.com/in-en)



TS 8610.805 - Glazed door for TS, TS IT, VX SE

Instead of a sheet steel door or rear panel.



Features

Model No.	TS 8610.805
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section
	Corner pieces: Die-cast zinc
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035
	Corner pieces: RAL 7035
	Viewing window (printed mask on the inside): RAL 9005
Supply includes	Viewing door frame with safety glass
	Locking rod with double-bit insert
	180° hinges (4)
Visible area	Viewing window width: 660 mm
	Viewing window height: 1,840 mm
Viewing window height	1,840 mm

© Rittal 2025

Features

Assembly instruction	Lock components are required when mounting instead of the rear
IP protection category to IEC 60 529	IP 55
To fit	Enclosure type: TS
	TS IT
	VX SE
	Width: = 800 mm
	Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	16
Gross weight	17
Customs tariff number	76101000
EAN	4028177693852
ETIM 9	EC000747
ECLASS 8.0	27182204

© Rittal 2025 3