

Rittal – The System.

Faster – better – everywhere.



TS 8612.760

TS punched rail 25 x 38 mm

State: 14/2/2026 (Source: ittal.com/in-en)



FRIEDHELM LOH GROUP

TS 8612.760 - TS punched rail 25 x 38 mm

For heavy installations, with attachment holes. Installation options on the vertical TS enclosure section.



Features

Model No.	TS 8612.760
Product description	For heavy installations, with attachment holes.
Material	Sheet steel, 3.0 mm
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section With 9 mm round holes all round on a 25 mm pitch pattern For the external mounting angle of support rails, system support rails, C rails 30/15, cable clamp rails (right angle section), own assemblies
Note	In conjunction with the snap-on nut, particularly well-suited for dynamic connections
To fit	Width/depth: 600 mm
Packs of	2 pc(s).
Net weight	1.648
Gross weight	1.96
Customs tariff number	73269098
EAN	4028177429147

Features

ECLASS 8.0

27189261