

Rittal – The System.

Faster – better – everywhere.



TS 8614.240 Partial mounting plates

State: 4/4/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8614.240 - Partial mounting plates for TS, VX SE

For universal interior installation and additional mounting levels.



Features

Model No.	TS 8614.240
Product description	For universal interior installation, also in conjunction with punched sections with mounting flanges and support strips. Defective assemblies are quickly and easily replaced. Additional mounting levels.
Material	Sheet steel, 2.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly parts
Note	Partial mounting plates are fastened directly onto the vertical enclosure sections via the inner mounting level using the assembly parts supplied loose. In this mounting position (in both the width and the depth) they form one level with TS punched sections with mounting flanges 17 x 73 mm and TS support strips for the inner mounting level.
Dimensions	Width: 1,100 mm Height: 300 mm

Features

To fit enclosure type	TS VX SE
To fit	Enclosure type: TS VX SE Width: = 400 mm = 1,200 mm Depth: = 400 mm
Packs of	1 pc(s).
Net weight	8.26 kg
Gross weight	8.46 kg
Customs tariff number	94039910
ETIM 9	EC000213
ECLASS 8.0	27409216
Product description	TS Partial mounting plate, for TS, SE, W/DH: 1100x300 mm