

# Rittal – The System.

Faster – better – everywhere.



## TS 8614.650 Partial mounting plates

State: 7/9/2025 (Source: [rittal.com/in-en](https://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8614.650 - Partial mounting plates for TS, VX SE

For universal interior installation and additional mounting levels.



## Features

Model No.	TS 8614.650
Product description	For universal interior installation, also in conjunction with punched sections with mounting flanges and support strips. Defective assemblies are quickly and easily replaced. Additional mounting levels.
Material	Sheet steel, 2.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly parts
Note	Partial mounting plates are fastened directly onto the vertical enclosure sections via the inner mounting level using the assembly parts supplied loose. In this mounting position (in both the width and the depth) they form one level with TS punched sections with mounting flanges 17 x 73 mm and TS support strips for the inner mounting level.
Dimensions	Width: 500 mm Height: 400 mm

# Features

To fit	Enclosure type: TS VX SE Width: = 600 mm Depth: = 500 mm = 600 mm
Packs of	1 pc(s).
Net weight	4.95
Gross weight	5.44
Customs tariff number	94039910
EAN	4028177212329
ETIM 9	EC000213
ECLASS 8.0	27409216