
Rittal - The System.

Faster – better – everywhere.





VX 8619.780


Punched section with mounting flange, 14 x 39 mm

State: 6/11/2025 (Source: rittal.com/in-en)



VX 8619.780 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.







Features

VX 8619.780
For attaching cable ducts, cable conduit holders, equipment installed on the door, etc.
Sheet steel
Zinc-plated
Assembly parts
1,275 mm
In enclosure height 1400 mm, in conjunction with rail for interior installation AX
In enclosure height 760 mm
For installation in AX sheet steel, only in conjunction with rail for interior installation AX
For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required

© Rittal 2025

Features

To fit	Enclosure type: AX Suitable for width or height or depth: 1,400 mm
Packs of	4 pc(s).
Net weight	2.44
Gross weight	2.7
Customs tariff number	73269098
EAN	4028177926844
E-Number Sweden	E3465286
ETIM 9	EC002620
ECLASS 8.0	27189234

© Rittal 2025 3