### Rittal – The System.

Faster – better – everywhere.





# VX 8640.032 Base/plinth trim panels, side, 100 mm

State: 3/12/2025 (Source: rittal.com/in-en)



# VX 8640.032 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

#### **Features**

Model No.	VX 8640.032
Product description	To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.
Material	Sheet steel
Colour	RAL 9005
Supply includes	Assembly parts
Dimensions	Height: 100 mm
To fit	Depth: = 500 mm
Type rating to UL 50E	Type 1, 12
Weight/pack	1.36 kg
Packs of	2 pc(s).
Net weight	1.16
Gross weight	1.36
Customs tariff number	94039910
EAN	4028177958944
E-Number Sweden	E3465378
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025 2

## Approvals

Approvals

UL + C-UL - FTTA

© Rittal 2025 3