

# Rittal – The System.

Faster – better – everywhere.



## TS 8800.620 EMC gland plate

State: 23/5/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8800.620 - EMC gland plate

For shielded cables with a maximum diameter of 20 mm in conjunction with standard gland plates.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | TS 8800.620  |
| Product description   | For shielded cables with a maximum diameter of 20 mm. Combined EMC contacting and cable fastening provide low-resistance contact between the cable shield and gland plate. For all 400, 500, 600 and 800 mm deep enclosures in conjunction with standard gland plates. |
| Material              | Sheet steel  |
| Surface finish        | Zinc-plated  |
| Supply includes       | Cable clamp strip with hammer-head punching<br>1 sliding gland plate<br>2 EMC seals  |
| Note on Model No.     | For one enclosure half only  |
| To fit                | Enclosure type: TS<br>Width: = 1,200 mm  |
| Note                  | Standard-compliant IP protection category not supported  |
| Packs of              | 1 pc(s).   |
| Net weight            | 1.825 kg   |
| Gross weight          | 2.025 kg   |
| Customs tariff number | 94039910   |
| ETIM 9                | EC002620   |
| ECLASS 8.0            | 27189261   |
| Product description   | TS EMC gland plate, W: 1200 mm   |