

Rittal – The System.

Faster – better – everywhere.



SV 9340.910 OM adaptors

State: 14/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.910 - OM adaptors with plug-in cable outlet



Features

Model No.	SV 9340.910
Design	with plug-in cable outlet
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Supply includes	Connector with connection facility for 3 main contacts (1.5 – 4 mm ²)
Rated current max.	25 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, 1 x TS 45D, 1 x TS 45D-V
Number of poles	3-pole
Connector outlet	Connector with connection facility for 3 main contacts (1.5 – 4 mm ²)
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 4 mm ²
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm

Features

Support frame (W x H)	45 mm x 170 mm
Packs of	1 pc(s).
Net weight	0.201 kg
Gross weight	0.289 kg
Copper weight (kg per piece)	0.025
Customs tariff number	85369095
ETIM 9	EC001531
ETIM 8	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 25 A, 690 V, 3-pole, with plug-in cable outlet, WH: 45x208 mm, support frame, support rail TS 45D, TS 45D-V

Approvals

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

OM adaptor 25 A

OM adaptor 25 A premium adaptor 3-pole
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 45 mm

Length: 208 mm

Support frame: 45 x 170 mm

Support frame support: -

PinBlock: -

Connector outlet: with connection facility
for 3 main contacts

Support rail: -

System:

Rittal RiLine60