

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.910 OM adaptors

State: 14/8/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.910 - OM adaptors with plug-in cable outlet



## Features

|   |   |
|---|---|
| Model No.                                     | SV 9340.910   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0                            |
| Colour  | Chassis: RAL 7035   |
| Supply includes                               | Connector with connection facility for 3 main contacts (1.5 – 4 mm <sup>2</sup> ) |
| Rated current max.                            | 25 A  |
| Rated operating voltage                       | 690 V, 3~   |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Support rail type                             | Support frame, 1 x TS 45D, 1 x TS 45D-V   |
| Number of poles                               | 3-pole  |
| Connector outlet                              | Connector with connection facility for 3 main contacts (1.5 – 4 mm <sup>2</sup> ) |
| Dimensions                                    | Width: 45 mm<br>Height: 208 mm  |
| Connection of round conductors                | 1.5 - 4 mm <sup>2</sup>   |
| Support rails Qty/height                      | 2 / 10 mm   |
| To fit busbars                                | Height: 5, 10 mm  |
| Support frame (W x H)                         | 45 mm x 170 mm  |

# Features

|                              |               |
|------------------------------|---------------|
| Packs of                     | 1 pc(s).      |
| Net weight                   | 0.201         |
| Gross weight                 | 0.289         |
| Copper weight (kg per piece) | 0.025         |
| Customs tariff number        | 85369095      |
| EAN                          | 4028177555464 |
| ETIM 9                       | EC001531      |
| ETIM 8                       | EC001531      |
| ECLASS 8.0                   | 27370304      |

# Approvals

|              |   |
|--------------|---|
| Approvals    | ABS<br>DNV-GL<br>Lloyds Register of Shipping              |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

# Tender text

OM adaptor 25 A

OM adaptor 25 A premium adaptor 3-pole

for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 45 mm

Length: 208 mm

Support frame: 45 x 170 mm

Support frame support: -

PinBlock: -

Connector outlet: with connection facility

for 3 main contacts

Support rail: -

System:

Rittal RiLine60