Rittal – The System.

Faster - better - everywhere.





SV 9342.004 Busbar support PLS

State: 31/10/2025 (Source: rittal.com/in-en)



SV 9342.004 - Busbar support PLS

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole, suitable for top-mounting.



Features

| Model No. | SV 9342.004 |
|-------------------------------------|--|
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Rated operating voltage | 1000 V, 3~ |
| Electrical ratings UL (SCCR) | 65 kA - 480 V, support spacing 250 mm, PLS 1600 busbars, circuit breaker max. 1200 A, DIVQ/7 |
| Note on Model No. | The use of a base tray is required for UL applications UL approval only applies in conjunction with AC application |
| Busbar support design | PLS 1600 PLUS |
| Number of poles | 4-pole |
| To fit busbars | PLS 1600 |
| Internal attachment | Yes |
| Centre-to-centre spacing of busbars | 60 mm |
| Packs of | 4 pc(s). |
| Net weight | 2.2 |
| Gross weight | 2.321 |

© Rittal 2025

Features

| Customs tariff number | 85469010 |
|-----------------------|---------------|
| EAN | 4028177536760 |
| ETIM 9 | EC001166 |
| ECLASS 8.0 | 27400607 |

Approvals

| Approvals | ABS Lloyds Register of Shipping UL + C-UL (listed) |
|--------------|--|
| Explanations | Declaration of conformity Declaration of conformity UK |

© Rittal 2025 3