

Rittal – The System.

Faster – better – everywhere.



SV 9345.704

Circuit-breaker component adaptor

State: 28/8/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.704 - Circuit-breaker component adaptor 4-pole

Features

Model No.	SV 9345.704
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	Copper spacer roll Connection screws Contact plates
Rated current max.	500 A
Rated operating voltage	690 V, 4~
Cable outlet	Bottom
For bar systems with centre-to-centre spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications
Number of poles	4-pole
Dimensions	Width: 185 mm Height: 300 mm
To fit busbars	Height: 5, 10 mm
To fit manufacturer (model)	ABB (Tmax T5)
Packs of	1 pc(s).
Net weight	3.98
Gross weight	4.027
Copper weight (kg per piece)	2.765
Customs tariff number	85369095
EAN	4028177684515

Features

ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---