

Rittal – The System.

Faster – better – everywhere.



SV 9635.210 Connection adaptor

State: 3/9/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.210 - Connection adaptor RiLine Compact

For connecting round conductors.

Features

Model No.	SV 9635.210
Function principle	To supply power to the board
Material	Polyamide Fire protection corresponding to UL 94
Colour	RAL 7035
Note	The technical data may vary for UL applications
Note on Model No.	Can be used as a central infeed or as a longitudinal connector for two bayed boards
Rated current max.	125 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Cable outlet	Top/bottom
Electrical ratings UL	Rated operating voltage (max.) UL: 600 V AC480 V AC
Type of electrical connection	Box terminal
Connection of round conductors, fine wire without wire end ferrule	6 - 50 mm ²
Connection of round conductors, fine wire with wire end ferrule	6 - 50 mm ²
Connection of round conductors, multi-wire	6 - 50 mm ²
Connection of round conductors, single-wire	6 - 50 mm ²
Connection for round conductor	AWG 1 - 10

Features

Dimensions	Width: 45 mm Height: 160 mm Depth: 92.5 mm
Packs of	4 pc(s).
Net weight	1.12
Gross weight	1.183
Copper weight (kg per piece)	0.04
Customs tariff number	85369010
EAN	4028177934603
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK