

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.350 Component adaptor

State: 8/7/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.350 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

## Features

|                              |  |
|------------------------------|--|
| Model No.                    | SV 9635.350  |
| Design                       | Comfort  |
| Function principle           | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material                     | Polyamide<br>Fire protection corresponding to UL 94                                  |
| Colour                       | RAL 7035   |
| Note                         | The technical data may vary for UL applications                                      |
| Rated current max.           | 32 A   |
| Rated operating voltage      | 600 V (DC), 3~<br>690 V (AC), 3~   |
| Number of poles              | 3-pole   |
| Electrical ratings UL        | Rated operating voltage (max.) UL: 600 V AC  |
| Connection cables (AWG)      | AWG 10   |
| Length of connection cable   | 160 mm   |
| Support rails Qty/height     | 1 / 10 mm  |
| Support rail type            | adjustable   |
| Dimensions                   | Width: 45 mm<br>Height: 160 mm<br>Depth: 34.5 mm                                     |
| Packs of                     | 4 pc(s).   |
| Net weight                   | 0.56 kg  |
| Gross weight                 | 0.582 kg   |
| Copper weight (kg per piece) | 0.055  |

# Features

---

|                       |  |
|-----------------------|--|
| Customs tariff number | 85369095   |
| ETIM 9                | EC001531   |
| ECLASS 8.0            | 27370304   |
| Product description   | SV Component adaptor (Comfort), 32 A, 690 V (AC), 600 V (DC), 3-pole, connection cable AWG 10 (L: 100 mm), WH: 45x160 mm |

---

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---