

Rittal – The System.

Faster – better – everywhere.



SV 9635.700 NH fuse-switch disconnecter

State: 3/7/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.700 - NH fuse-switch disconnecter Size 000

For RiLine Compact busbar system.



Features

| | |
|-------------------------------|---|
| Model No. | SV 9635.700 |
| Function principle | To protect connected equipment Integral test holes provide measurement access to the contact parts of the fuse inserts For cable outlet at the top, the NH fuse-switch disconnecter must be mounted on the board rotated through 180° |
| Material | Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper |
| Colour | RAL 7035 |
| Test specification | IEC/DIN EN 60 947-3 |
| For NH size | 000 |
| Rated operating current max. | 125 A |
| Rated operating voltage | 440 V (DC), 3~ 690 V (AC), 3~ |
| Number of poles | 3-pole |
| Cable outlet | Top/bottom |
| Type of electrical connection | Box terminal |

Features

| | |
|---|--|
| Connection of round conductors | 2.5 - 50 mm ² |
| Clamping area for laminated copper bars (W x H) | 10 x 10 mm |
| Dimensions | Width: 49.5 mm Height: 174.5 mm Depth: 96 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.52 kg |
| Gross weight | 0.562 kg |
| Copper weight (kg per piece) | 0.145 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001040 |
| ECLASS 8.0 | 27371401 |
| Product description | LV HRC fused interrupter, size 000, 690 V (RiLine Compact) |