

Rittal – The System.

Faster – better – everywhere.



SV 9677.770 Component adaptor

State: 23/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.770 - Component adaptor clamping attachment

For circuit-breakers from ABB, Eaton, Schneider Electric and Siemens. For bar systems with 185 mm centre-to-centre spacing.

Features

Model No.	SV 9677.770
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	Connection straps
For bar systems with centre-to-centre spacing	185 mm
Cable outlet	Bottom
Installation type	Clamping attachment
Number of poles	3-pole
Rated current max.	630 A
Rated operating voltage	690 V, 3~
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal For mounting on busbar systems with or without cover section
Dimensions	Width: 150 mm Height: 585 mm
To fit busbars	Height: 10 mm
To fit manufacturer (model)	ABB (Tmax T5) Eaton (NZM3) Schneider Electric (NSX630) Siemens (3VA23, 3VA24, 3VL4)
Packs of	1 pc(s).
Net weight	6.2 kg

Features

Gross weight	6.629 kg
Copper weight (kg per piece)	3.754
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Component adaptor, 630 A, 690 V, 3-pole, 185 mm, clamping attachment

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK