

Rittal – The System.

Faster – better – everywhere.



underlined 9792.101

Ex enclosures

State: 19/12/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 9792.101 - Ex enclosures stainless steel, empty enclosure with hinged door

Features

Model No.	9792.101
Benefits	Zone 1 and 2 or 21 and 22 to 2014/34/EC Protection type to EN 60 079: Equipment protection due to increased safety, equipment protection due to enclosure
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Sheet steel, zinc-plated
Surface finish	Enclosure: Outside 4B, Inside 2B Mounting plate: Sheet steel, zinc-plated
Supply includes	Enclosure Door Mounting plate
Dimensions	Width: 200 mm Height: 300 mm Depth: 150 mm
Dimensions mounting plate (W x H)	145 mm x 245 mm
Material thickness - enclosure	2 mm
Material thickness of mounting plate	3 mm
Material thickness - door	2 mm
Lock	Lock version: Cam lock with 3 mm double-bit lock insert Number of locks: 1
IP protection category to IEC 60 529	IP 66
Operating temperature range	-50 °C...180 °C

Features

Operating temperature	The specified temperatures may be limited by the installed equipment
Packs of	1 pc(s).
Net weight	0.01
Gross weight	0.01
EAN	4028177979468

Approvals

Approvals	ATEX IECEX
-----------	---------------