


Rittal – The System.

Faster – better – everywhere.



TS 4696.000

サポートレール

State: 2025/05/16 (Source: [rittal.com/jp-ja](https://www.rittal.com/jp-ja))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4696.000 - サポートレール VX、TS、VX SE、TP、AX 用

ケーブルダクト、ケーブルダクトホルダー、接触防止カバー、ドアへの実装機器およびケーブル取り付け用アクセサリを簡単に固定するために使用します。



Features

品番	TS 4696.000
製品説明	ケーブルダクト、ケーブルダクトホルダー、接触防止カバー、ドアへの実装機器およびケーブル取り付け用アクセサリを簡単に固定するために使用します。
仕様	穴Ø 4.5 mm、25 mm ピッチ
材質	鋼板製
表面	亜鉛めっき
同梱品	取り付け部品を含む
長さ	540 mm
取り付け方法 VX	In enclosure width/depth 600 mm
取り付け方法、VX SE	In enclosure width/depth 600 mm, on the outer mounting level
取り付け方法 AX	In door width 600 mm, with cam lock In door width 600 mm, with 3-point lock system, in the hinged door

Features

AX stainless steel installation options	In door width 600 mm, in hinged door, in conjunction with the perforated door strip
取り付け方法 PC	In enclosure width 600 mm, on the outer mounting level
取り付け方法 IW	In enclosure width/depth 600 mm, on the outer mounting level
取り付け方法 TS	In enclosure width/depth 600 mm, on the outer mounting level
取り付け方法 AE	In enclosure width/height 600 mm, in conjunction with rail for interior installation AE
取り付け方法 TP	In consoles for 3-part assembly, at the height of the enclosure cover, in conjunction with rail for interior installation for TP, compact enclosure HD
VX base/plinth installation options	In base/plinth width/depth 600 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket
適用	<p>エンクロージャータイプ: VX</p> <p>TS</p> <p>VX SE</p> <p>TP</p> <p>PC</p> <p>IW</p> <p>AX</p> <p>AE</p> <p>適用幅/奥行: 600 mm</p>
適用	VX ベースシステム
1パック	20 個
純質量	5.22
総質量	5.54
PCF per pack (cradle-to-gate)	21.2 kg CO2 eq (Cat B)

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
関税率番号	73269098
EAN	4028177108158
E-Number Sweden	E3465252
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261