## Rittal - The System.

Faster – better – everywhere.





# IT 5302.042 19インチ ケーブルブリッジ、奥行 き可変式

State: 2025/11/26 (Source: rittal.com/jp-ja)



## IT 5302.042 - 19インチ ケーブルブリッジ、奥行き可変式

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

#### **Features**

品番	IT 5302.042
メリット	Cable entry at the front via brush strip for thermal partitioning of the cable entry zone  Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear  Fully depth-variable with versatile, infinitely adjustable extension of the cable link  Prevents incorrect airflow by partitioning the transition  Open at the top for easy retrofitting, even with cables already inserted  Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip
材質	鋼板製 ブラシストリップ:プラスチック(UL 94-V0準拠)
表面	
塗装色	RAL 9005
同梱品	Cable link ブラシストリップ
取り付け方法	フロント側とリア側の 19インチ機器取り付け面 間の固定に使用し ます
取り付け面間隔	500 - 750 mm

© Rittal 2025

2

#### **Features**

高さ単位(ユニット)	1 U
耐荷重(静荷重)	150 N
適用	全エンクロージャー対応
注記:	Assembly parts should be ordered separately
1パック	1個
関税率番号	73269098

© Rittal 2025 3