

Rittal – The System.

Faster – better – everywhere.



IT 5302.042

19インチ ケーブルブリッジ、奥行き可変式

State: 2026/02/10 (Source: [ittal.com/jp-ja](https://www.ittal.com/jp-ja))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 5302.042 - 19インチ ケーブルブリッジ、奥行き可変式

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

Features

品番	IT 5302.042
メリット	<p>Cable entry at the front via brush strip for thermal partitioning of the cable entry zone</p> <p>Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear</p> <p>Fully depth-variable with versatile, infinitely adjustable extension of the cable link</p> <p>Prevents incorrect airflow by partitioning the transition</p> <p>Open at the top for easy retrofitting, even with cables already inserted</p> <p>Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip</p>
材質	<p>鋼板製</p> <p>ブラシストリップ：プラスチック (UL 94-V0準拠)</p>
表面	塗装
塗装色	RAL 9005
同梱品	<p>Cable link</p> <p>ブラシストリップ</p>
取り付け方法	フロント側とリア側の 19インチ機器取り付け面 間の固定に使用します
取り付け面間隔	500 - 750 mm

Features

高さ単位(ユニット)	1 U
耐荷重(静荷重)	150 N
適用	全エンクロージャー対応
注記：	Assembly parts should be ordered separately
1パック	1 個
PCF/VE (Cradle to Gate)	PCF-Wert 18,78 kg Co ² e
関税率番号	73269098