


Rittal – The System.

Faster – better – everywhere.



CX 6704.000 CX ベースユニット

State: 2026/01/16 (Source: rittal.com/jp-ja)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

CX 6704.000 - CX ベースユニット

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



Features

品番	CX 6704.000
仕様	ベースユニット
材質	エンクロージャー：鋼板 1.5 mm ドア：鋼板製、2.0 mm、周囲に発泡ポリウレタンパッキンを塗布 マウンティングプレート：鋼板製、2.5 mm
表面	エンクロージャーとドア：電着浸漬下塗り、外側は静電粉体塗装、 凹凸模様（テクスチャー）仕上げ マウンティングプレート：亜鉛めっき
塗装色	RAL 7035
同梱品	エンクロージャー、上部オープン フロントドアおよびフロント両開きドア、3点ロックシステム付き マウンティングプレート グランドプレート ロック：ダブルビットNo.5/3 mm

Features

寸法：	幅: 600 mm 高さ: 675 mm 奥行: 500 mm
マウンティングプレートの寸法 (幅 x 高さ)	520 mm x 625 mm
ドアの数	1
ドア開角度	130°
IKコード	IK10
注記：	ベースユニットを塞ぐためには、エンドプレート (カバー) が必要です 2 パーツ構成のコンソールには、デスクユニットとデスクユニット用のエンドプレート (カバー) が必要です 3 パーツ構成のコンソールには、デスクユニットとコンソールユニットが必要です
保護等級 IP (IEC 60 529 準拠)	IP 55
Protection category NEMA	NEMA 1 NEMA 12
基材	鋼板製
ロックの数	1
ロックの仕様	3点ロックシステム
ロックインサート	ダブルビット 3 mm
ロック	ロックの仕様: 3点ロックシステム ロックの数: 1 ロックインサート: ダブルビット 3 mm
1パック	1 個
純質量	34

Features

総質量	35.75
関税率番号	94032080
EAN	4028177983762
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	UL + C-UL (listed)
Explanations	CE適合宣言書