


Rittal – The System.

Faster – better – everywhere.



RX 9360.513 RiLineX Circuit-breaker component adaptor

State: 2025/08/02 (Source: rittal.com/jp-ja)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.513 - RiLineX Circuit-breaker component adaptor

CB component adaptors for the RiLineX busbar platform in widths 81 to 140 mm. For mounting moulded-case circuit-breakers (MCCBs). Products are available in two variants: An "Easy-Fix" variant for user-friendly external mounting of switches from all standard manufacturers, and a "Universal" variant with U nuts for maximum flexibility.

Features

品番	RX 9360.513
仕様	Easy Fix
メリット	コンパクト サーキットブレーカー (MCCB) をボード上に直接設置 Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
材質	ポリアミド (PA 6) 耐燃性 UL 94 適合
塗装色	RAL 9005 RAL 35745
保護等級 IP (IEC 60 529 準拠)	IP 2XB
定格電流 最大	250 A
定格電流 (UL)	210 A
定格インパルス電圧 Uimp	12 kV
定格電圧	690 V AC 690 V DC 600 V AC (UL)

Features

Rated insulation voltage	1,000 V
過電圧カテゴリー	4
汚染度	3
極数	3 極
ケーブル引き出し口	上
電源接続	ねじ M8
適用バスバーシステム	RiLineX RiLine60
基本周波数	50...60 Hz
湿度(結露無きこと)	10...90 %
適用バスバー	15 x 5/10 20 x 5/10 30 x 5/10
動作温度範囲	-25 °C...55 °C
保管温度範囲	-25 °C...75 °C
寸法：	幅: 105 mm 高さ: 252 mm 奥行: 63 mm
1パック	1 個

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------